

Hurd Clad Wood Products That Qualify for 2009/2010 Tax Credit

6/3/2010

PRODUCT/GLAZING MAKE-UP	U-FACTOR	SHGC	VT	CR	QUALIFIES FOR TAX CREDIT
<b>Energy Plus Clad Casement Rectangular Units (3/4" IG) -- Must select "Energy Plus" under frame type in E-Bid</b>					
Insul--LE/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.26	0.45	56	X
Insul--LE/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL< 1") <sup>2</sup>	0.30	0.24	0.41	56	X
Insul--LE SPF/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.25	0.44	56	X
Insul--LE SPF/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL< 1") <sup>2</sup>	0.30	0.23	0.40	56	X
Insul--Climate Control LE/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.24	0.44	56	X
Insul--Climate Control LE/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL<1") <sup>2</sup>	0.30	0.22	0.40	56	X
Insul--Climate Control LE SPF/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.24	0.43	56	X
Insul--Climate Control LE SPF/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL<1") <sup>2</sup>	0.30	0.22	0.39	56	X
Insul--Super Sunblocker LE/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.19	0.35	56	X
Insul--Super Sunblocker LE/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL<1") <sup>2</sup>	0.30	0.17	0.31	56	X
Insul--Super Sunblocker LE SPF/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.18	0.34	56	X
Insul--Super Sunblocker LE SPF/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL<1") <sup>2</sup>	0.30	0.17	0.31	56	X
Insul--Cardinal 366 LE/CL Argon-Filled <sup>1</sup>	0.30	0.18	0.41	58	X
Insul--Cardinal 366 LE/CL Argon-Filled (w/GIAS or CHDL< 1") <sup>1</sup>	0.30	0.17	0.37	58	X
<sup>1</sup> This product requires you to choose "Energy Plus" under frame type					
<sup>2</sup> This product requires you to choose "Energy Plus" under frame type and comment "w/SS Spacer and Argon"					

<b>Energy Plus Clad Casement Rectangular Units (1" Triple IG--Not Available With GIAS or Internal CHDL Spacer Bar) -- Must select "Energy Plus" under frame type in E-Bid</b>					
Triple IG--LE/CL/LE Air <sup>3</sup> -- Produced with capillary tubes	0.30	0.21	0.35	63	X
Triple IG--LE/CL/LE Air-Filled (CHDL< 1" w/o internal spacer) -- Produced with capillary tubes	0.30	0.19	0.31	63	X
Triple IG--LE/CL/CL Argon-Filled <sup>4</sup>	0.30	0.23	0.41	62	X
Triple IG--LE/CL/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.21	0.37	62	X
Triple IG--LE/CL/LE Argon-Filled <sup>4</sup>	0.27	0.21	0.35	64	X
Triple IG--LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.27	0.19	0.31	64	X
<sup>1</sup> This product requires you to choose "Energy Plus" under frame type. Note--CHDL in Triple IG cannot be ordered with internal spacer.					

<b>Energy Saver Clad Casement Rectangular and Arch Top Units (1" Triple IG -- Not Available With GIAS or Internal CHDL Spacer Bar)</b>					
Triple IG--LE/CL/LE Argon-Filled	0.28	0.21	0.35	64	X
Triple IG--LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.28	0.19	0.31	64	X
Note--CHDL in Triple IG cannot be ordered with internal spacer.					

<b>Energy Plus Clad Awning (3/4" IG) -- Must select "Energy Plus" under frame type in E-Bid</b>					
Insul--LE/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.26	0.47	54	X
Insul--LE/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL< 1") <sup>2</sup>	0.30	0.24	0.42	54	X
Insul--LE SPF/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.26	0.46	54	X
Insul--LE SPF/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL< 1") <sup>2</sup>	0.30	0.24	0.41	54	X
Insul--Climate Control LE/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.25	0.46	54	X
Insul--Climate Control LE/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL<1") <sup>2</sup>	0.30	0.23	0.41	54	X
Insul--Climate Control LE SPF/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.24	0.45	54	X
Insul--Climate Control LE SPF/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL<1") <sup>2</sup>	0.30	0.22	0.40	54	X
Insul--Super Sunblocker LE/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.19	0.36	55	X
Insul--Super Sunblocker LE/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL<1") <sup>2</sup>	0.30	0.17	0.32	55	X
Insul--Super Sunblocker LE SPF/CL Argon-Filled w/Stainless Steel Spacer <sup>2</sup>	0.30	0.19	0.35	54	X
Insul--Super Sunblocker LE SPF/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL<1") <sup>2</sup>	0.30	0.17	0.32	54	X
Insul--Cardinal 366 LE/CL Argon-Filled <sup>1</sup>	0.29	0.19	0.43	56	X
Insul--Cardinal 366 LE/CL Argon-Filled (w/GIAS or CHDL< 1") <sup>1</sup>	0.29	0.17	0.38	56	X
<sup>1</sup> This product requires you to choose "Energy Plus" under frame type					
<sup>2</sup> This product requires you to choose "Energy Plus" under frame type and comment "w/SS Spacer and Argon"					

<b>Energy Plus Clad Awning (1" Triple IG -- Not Available With GIAS or Internal CHDL Spacer Bar) -- Must select "Energy Plus" under frame type in E-Bid</b>					
Triple IG--LE/CL/LE Air-Filled <sup>3</sup> -- Produced with capillary tubes	0.28	0.21	0.36	62	X
Triple IG--LE/CL/LE Air-Filled (CHDL< 1" w/o internal spacer) -- Produced with capillary tubes	0.28	0.20	0.32	62	X
Triple IG--LE/CL/CL Argon-Filled <sup>4</sup>	0.29	0.23	0.42	61	X
Triple IG--LE/CL/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.29	0.21	0.38	61	X
Triple IG--LE/CL/LE Argon-Filled <sup>4</sup>	0.25	0.21	0.36	65	X
Triple IG--LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.25	0.20	0.32	65	X
<sup>1</sup> This product requires you to choose "Energy Plus" under frame type. Note--CHDL in Triple IG cannot be ordered with internal spacer.					

Hurd Clad Wood Products That Qualify for 2009/2010 Tax Credit

PRODUCT/GLAZING MAKE-UP	U-FACTOR	SHGC	VT	CR	QUALIFIES FOR TAX CREDIT
<b>Energy Saver Clad Awning (1" Triple IG -- Not Available With GIAS or Internal HDL Spacer Bar)</b>					
Triple IG--LE/CL/LE Air-Filled -- Produced with capillary tubes	0.30	0.21	0.36	62	X
Triple IG--LE/CL/LE Air-Filled (CHDL< 1" w/o internal spacer) -- Produced with capillary tubes	0.30	0.20	0.32	62	X
Triple IG -- LE/CL/LE Argon-Filled	0.27	0.21	0.36	65	X
Triple IG--LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.27	0.20	0.32	65	X
<i>Note--CHDL in Triple IG cannot be ordered with internal spacer.</i>					

<b>Energy Plus Clad Casement Picture (3/4" IG) -- Must select "Energy Plus" under frame type in E-Bid</b>					
Insul LE/CL Argon-Filled <sup>d</sup>	0.30	0.30	0.54	53	X
Insul LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.28	0.48	53	X
Insul LE SPF/CL Argon-Filled <sup>d</sup>	0.30	0.30	0.53	54	X
Insul LE SPF/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.27	0.47	53	X
Insul--Climate Control LE/CL Argon-Filled <sup>d</sup>	0.30	0.29	0.53	53	X
Insul--Climate Control LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.26	0.47	53	X
Insul--Climate Control SPF LE/CL Argon-Filled <sup>d</sup>	0.30	0.28	0.52	54	X
Insul--Climate Control SPF LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.26	0.46	54	X
Insul--Super Sunblocker LE/CL Argon-Filled <sup>d</sup>	0.30	0.22	0.41	53	X
Insul--Super Sunblocker LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.20	0.37	53	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled <sup>d</sup>	0.30	0.22	0.41	54	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.20	0.36	54	X
Insul--Cardinal 366 LE/CL Argon-Filled <sup>d</sup>	0.29	0.22	0.49	59	X
Insul--Cardinal 366 LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.29	0.20	0.44	54	X
<sup>f</sup> This product requires you to choose "Energy Plus" under frame type.					

<b>Energy Plus Clad Casement Picture (1" Triple IG Not Available With GIAS or Internal Spacer Bar; Sizes Limited) -- Must select "Energy Plus" under frame type in E-Bid</b>					
Triple IG--LE/CL/LE Air-Filled <sup>d</sup> -- Produced with capillary tubes	0.29	0.25	0.41	58	X
Triple IG--LE/CL/LE Air-Filled (CHDL< 1" w/o internal spacer) <sup>f</sup> -- Produced with capillary tubes	0.29	0.22	0.37	58	X
Triple IG--LE/CL/CL Argon-Filled <sup>d</sup>	0.29	0.27	0.49	58	X
Triple IG--LE/CL/CL Argon-Filled (CHDL< 1" w/o internal spacer) <sup>f</sup>	0.29	0.24	0.43	58	X
Triple IG--LE/CL/LE Argon-Filled <sup>d</sup>	0.25	0.24	0.41	62	X
Triple IG--LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer) <sup>f</sup>	0.25	0.22	0.37	62	X
<sup>f</sup> This product requires you to choose "Energy Plus" under frame type. Note--CHDL in Triple IG cannot be ordered with internal spacer.					

<b>Energy Plus Clad Casement Sash &amp; Frame (3/4" IG) -- Must select "Energy Plus" under frame type in E-Bid</b>					
Insul LE/CL Argon-Filled <sup>d</sup>	0.30	0.30	0.54	53	X
Insul LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.28	0.48	53	X
Insul LE SPF/CL Argon-Filled <sup>d</sup>	0.30	0.30	0.53	54	X
Insul LE SPF/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.27	0.47	53	X
Insul--Climate Control LE/CL Argon-Filled <sup>d</sup>	0.30	0.29	0.53	53	X
Insul--Climate Control LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.26	0.47	53	X
Insul--Climate Control SPF LE/CL Argon-Filled <sup>d</sup>	0.30	0.28	0.52	54	X
Insul--Climate Control SPF LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.26	0.46	54	X
Insul--Super Sunblocker LE/CL Argon-Filled <sup>d</sup>	0.30	0.22	0.41	53	X
Insul--Super Sunblocker LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.20	0.37	53	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled <sup>d</sup>	0.30	0.22	0.41	54	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.30	0.20	0.36	54	X
Insul--Cardinal 366 LE/CL Argon-Filled <sup>d</sup>	0.29	0.22	0.49	59	X
Insul--Cardinal 366 LE/CL Argon-Filled (GIAS or CHDL< 1") <sup>f</sup>	0.29	0.20	0.44	54	X
<sup>f</sup> This product requires you to choose "Energy Plus" under frame type.					

<b>Energy Plus Clad Casement Sash &amp; Frame (1" Triple IG Not Available With GIAS or Internal HDL Spacer Bar) -- Must select "Energy Plus" under frame type in E-Bid</b>					
Triple IG--LE/CL/LE Air-Filled <sup>d</sup> -- Produced with capillary tubes	0.29	0.25	0.41	58	X
Triple IG--LE/CL/LE Air-Filled (CHDL< 1" w/o internal spacer) <sup>f</sup> -- Produced with capillary tubes	0.29	0.22	0.37	58	X
Triple IG--LE/CL/CL Argon-Filled <sup>d</sup>	0.29	0.27	0.49	58	X
Triple IG--LE/CL/CL Argon-Filled (CHDL< 1" w/o internal spacer) <sup>f</sup>	0.29	0.24	0.43	58	X
Triple IG--LE/CL/LE Argon-Filled <sup>d</sup>	0.25	0.24	0.41	62	X
Triple IG--LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer) <sup>f</sup>	0.25	0.22	0.37	62	X
<sup>f</sup> This product requires you to choose "Energy Plus" under frame type. Note--CHDL in Triple IG cannot be ordered with internal spacer.					

Hurd Clad Wood Products That Qualify for 2009/2010 Tax Credit

PRODUCT/GLAZING MAKE-UP	U-FACTOR	SHGC	VT	CR	QUALIFIES FOR TAX CREDIT
<b>Energy Saver Clad Casement Picture (3/4" IG)</b>					
Insul--LE/CL Argon-Filled w/Stainless Steel Spacer <sup>1</sup>	0.30	0.30	0.54	56	X
Insul--LE/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL < 1")	0.30	0.28	0.48	55	X
Insul--LE SPF/CL Argon-Filled w/Stainless Steel Spacer <sup>1</sup>	0.30	0.30	0.53	56	X
Insul--LE SPF/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL < 1")	0.30	0.27	0.47	56	X
Insul--Super Sunblocker LE/CL Argon-Filled w/Stainless Steel Spacer <sup>1</sup>	0.30	0.22	0.41	56	X
Insul--Super Sunblocker LE/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL < 1")	0.30	0.20	0.37	55	X
Insul--Super Sunblocker LE SPF/CL Argon-Filled w/Stainless Steel Spacer <sup>1</sup>	0.30	0.22	0.41	56	X
Insul--Super Sunblocker LE SPF/CL Argon-Filled w/Stainless Steel Spacer (w/GIAS or CHDL < 1")	0.30	0.20	0.36	56	X
Insul--Cardinal 366 LE/CL Argon-Filled	0.30	0.22	0.49	59	X
Insul--Cardinal 366 LE/CL Argon-Filled (w/GIAS or CHDL < 1")	0.30	0.20	0.44	58	X
<sup>2</sup> This product requires you to choose or comment "w/SS Spacer and Argon"					
<b>Energy Saver Clad Casement Picture (1" Triple IG -- Not Available With GIAs or Internal Spacer Bar; Limited Sizes Available)</b>					
Triple IG--LE/CL/CL Argon-Filled	0.30	0.27	0.49	58	X
Triple IG--LE/CL/CL Argon-Filled (CHDL < 1" w/o internal spacer)	0.30	0.24	0.43	58	X
Triple IG--LE/CL/LE Argon-Filled	0.26	0.24	0.41	61	X
Triple IG--LE/CL/LE Argon-Filled (CHDL < 1" w/o internal spacer)	0.26	0.22	0.37	61	X
Note--CHDL in Triple IG cannot be ordered with internal spacer.					
<b>Premium Clad DH Operator (3/4" IG)</b>					
Insul LE/CL Air-Filled W/Storm (With GIA or CHDL < 1" ) -- Produced with capillary tubes	0.27	0.26	0.41	62	X
Insul LE/CL Air-Filled W/Storm -- Produced with capillary tubes	0.27	0.29	0.46	62	X
Insul LE/CL Air-Filled W/Storm (With GIA or CHDL < 1" ) -- Produced with capillary tubes	0.27	0.26	0.41	62	X
Insul Climate Control LE/CL Air-Filled W/Storm -- Produced with capillary tubes	0.27	0.27	0.45	62	X
Insul Climate Control LE/CL Air-Filled W/Storm (With GIA or CHDL < 1" ) -- Produced with capillary tubes	0.27	0.25	0.40	62	X
Insul--Super Sunblocker LE/CL Air-Filled W/Storm -- Produced with capillary tubes	0.27	0.23	0.35	62	X
Insul--Super Sunblocker LE/CL Air-Filled W/Storm (With GIA or CHDL < 1" ) -- Produced with capillary tubes	0.27	0.21	0.31	62	X
Insul Solar Ban 70 LE/CL Argon-Filled -- Produced with Technoform Stainless Steel Spacer <sup>1</sup>	0.30	0.20	0.45	62	X
Insul Solar Ban 70 LE/CL Argon-Filled (With GIA or CHDL < 1" ) -- Produced with Technoform Stainless Steel Spacer <sup>1</sup>	0.30	0.18	0.40	62	X
Insul LE/CL Argon-Filled W/Storm	0.25	0.28	0.46	64	X
Insul LE/CL Argon-Filled W/Storm (With GIA or CHDL < 1" )	0.25	0.25	0.41	63	X
Insul Climate Control LE/CL Argon-Filled W/Storm	0.25	0.27	0.45	63	X
Insul Climate Control LE/CL Argon-Filled W/Storm (With GIA or CHDL < 1" )	0.25	0.24	0.40	63	X
Insul--Super Sunblocker LE/CL Argon-Filled W/Storm	0.24	0.22	0.35	64	X
Insul--Super Sunblocker LE/CL Argon-Filled W/Storm (With GIA or CHDL < 1" )	0.24	0.20	0.31	63	X
Insul--Cardinal LE/CL Argon-Filled W/Storm	0.24	0.21	0.42	68	X
Insul--Cardinal LE/CL Argon-Filled W/Storm (With GIA or CHDL < 1" )	0.24	0.19	0.37	68	X
<sup>1</sup> This product requires you to choose or comment "w/Technoform SS Spacer and Argon"					

Hurd Clad Wood Products That Qualify for 2009/2010 Tax Credit

PRODUCT/GLAZING MAKE-UP	U-FACTOR	SHGC	VT	CR	QUALIFIES FOR TAX CREDIT
<b>Premium Clad DH Sash Kits (3/4" IG)</b>					
Insul LE/CL Air-Filled W/Storm -- Produced with capillary tubes	0.25	0.29	0.46	62	X
Insul LE/CL Air-Filled W/Storm (With GIA or CHDL < 1" ) -- Produced with capillary tubes	0.25	0.26	0.41	62	X
Insul Climate Control LE/CL Air-Filled W/Storm -- Produced with capillary tubes	0.25	0.27	0.45	62	X
Insul Climate Control LE/CL Air-Filled W/Storm (With GIA or CHDL < 1" ) -- Produced with capillary tubes	0.25	0.24	0.40	62	X
Insul--Super Sunblocker LE/CL Air-Filled W/Storm -- Produced with capillary tubes	0.25	0.23	0.35	62	X
Insul--Super Sunblocker LE/CL Air-Filled W/Storm (With GIA or CHDL < 1" ) -- Produced with capillary tubes	0.25	0.21	0.31	62	X
Insul--Cardinal LE/CL Air-Filled W/Storm -- Produced with capillary tubes	0.24	0.22	0.42	66	X
Insul--Cardinal LE/CL Air-Filled W/Storm (With GIA or CHDL < 1" ) -- Produced with capillary tubes	0.24	0.20	0.37	66	X
Insul LE/CL Argon-Filled Produced With Technoform Stainless Steel Spacer <sup>†</sup>	0.30	0.28	0.50	59	X
Insul LE/CL Argon-Filled Produced With Technoform Stainless Steel Spacer <sup>†</sup> (With GIA or CHDL < 1" )	0.30	0.25	0.45	59	X
Insul--Super Sunblocker LE/CL Argon-Filled Produced With Technoform Stainless Steel Spacer <sup>†</sup>	0.30	0.20	0.29	59	X
Insul--Super Sunblocker LE/CL Argon-Filled Produced With Technoform Stainless Steel Spacer <sup>†</sup> (With GIA or CHDL < 1" )	0.30	0.18	0.34	59	X
Insul--Cardinal 366 LE/CL Argon-Filled	0.30	0.20	0.46	58	X
Insul--Cardinal 366 LE/CL Argon-Filled (With GIA or CHDL < 1" )	0.30	0.18	0.41	58	X
Insul LE/CL Argon-Filled W/Storm	0.23	0.28	0.46	64	X
Insul LE/CL Argon-Filled W/Storm (With GIA or CHDL < 1" )	0.23	0.25	0.41	64	X
Insul Climate Control LE/CL Argon-Filled W/Storm	0.23	0.27	0.45	64	X
Insul Climate Control LE/CL Argon-Filled W/Storm (With GIA or CHDL < 1" )	0.23	0.24	0.40	64	X
Insul--Super Sunblocker LE/CL Argon-Filled W/Storm	0.23	0.22	0.35	64	X
Insul--Super Sunblocker LE/CL Argon-Filled W/Storm (With GIA or CHDL < 1" )	0.23	0.20	0.31	64	X
Insul--Cardinal LE/CL Argon-Filled W/Storm	0.22	0.21	0.42	68	X
Insul--Cardinal LE/CL Argon-Filled W/Storm (With GIA or CHDL < 1" )	0.22	0.20	0.37	68	X
<sup>†</sup> This product requires you to choose or comment "w/Technoform SS Spacer and Argon"					

<b>Premium Clad DH Picture (3/4" IG)</b>					
Insul LE/CL Argon-Filled	0.30	0.29	0.52	56	X
Insul LE/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.27	0.46	56	X
Insul LE SPF/CL Argon-Filled	0.30	0.29	0.51	57	X
Insul LE SPF/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.26	0.45	57	X
Insul--Climate Control LE/CL Argon-Filled	0.30	0.28	0.51	56	X
Insul--Climate Control LE/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.25	0.45	56	X
Insul--Climate Control SPF LE/CL Argon-Filled	0.30	0.27	0.50	56	X
Insul--Climate Control SPF LE/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.24	0.44	56	X
Insul--Super Sunblocker LE/CL Argon-Filled	0.30	0.21	0.40	56	X
Insul--Super Sunblocker LE/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.19	0.36	56	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled	0.30	0.21	0.39	57	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.19	0.35	57	X
Insul--Cardinal 366 LE/CL Argon-Filled	0.29	0.21	0.47	60	X
Insul--Cardinal 366 LE/CL Argon-Filled (With GIA or CHDL)	0.29	0.19	0.42	60	X
<i>Note--CHDL in this product cannot be ordered with internal spacer as it will not meet the tax credit requirements</i>					

<b>Premium Clad DH Picture (1" Triple IG -- Not Available With GIAs or Internal Spacer Bar; Limited Sizes Available)</b>					
Triple IG--LE/CL/CL Air-Filled -- Produced w/capillary tubes	0.30	0.26	0.48	60	X
Triple IG--LE/CL/CL Air-Filled (CHDL w/o internal spacer) -- Produced w/capillary tubes	0.30	0.24	0.43	60	X
Triple IG--LE/CL/LE Air-Filled -- Produced w/capillary tubes	0.26	0.24	0.41	61	X
Triple IG--LE/CL/LE Air-Filled (CHDL w/o internal spacer) -- Produced w/capillary tubes	0.26	0.21	0.36	61	X
Triple IG--LE/CL/CL Argon-Filled	0.27	0.26	0.48	61	X
Triple IG--LE/CL/CL Argon-Filled (CHDL w/o internal spacer)	0.27	0.23	0.43	61	X
Triple IG--LE/CL/LE Argon-Filled	0.23	0.24	0.41	61	X
Triple IG--LE/CL/LE Argon-Filled (CHDL w/o internal spacer)	0.23	0.21	0.36	61	X
<i>Note--Values shown reflect SHGC and VT for CHDL &lt; 1". Wider bars also meet the .30/.30 requirement. CHDL in Triple IG cannot be ordered with internal spacer.</i>					

<b>Premium Clad DH Sash &amp; Frame (3/4" IG)</b>					
Insul LE/CL Argon-Filled	0.30	0.30	0.52	54	X
Insul LE/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.27	0.46	54	X
Insul--Super Sunblocker LE/CL Argon-Filled	0.30	0.21	0.40	54	X
Insul--Super Sunblocker LE/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.19	0.36	54	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled	0.30	0.21	0.40	55	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.19	0.36	54	X
Insul--Cardinal 366 LE/CL Argon-Filled	0.29	0.21	0.48	60	X
Insul--Cardinal 366 LE/CL Argon-Filled (With GIA or CHDL)	0.29	0.19	0.42	60	X
<i>Note--CHDL in this product cannot be ordered with internal spacer as it will not meet the tax credit requirements</i>					

Hurd Clad Wood Products That Qualify for 2009/2010 Tax Credit

PRODUCT/GLAZING MAKE-UP	U-FACTOR	SHGC	VT	CR	QUALIFIES FOR TAX CREDIT
<b>Monument Slider (1" Triple IG -- Not Available With GIAS or Internal HDL Spacer Bar; Some Size Limitations Apply)</b>					
Triple IG -- LE/CL/LE Air-Filled -- Produced with capillary tubes	0.29	0.24	0.40	59	X
Triple IG -- LE/CL/LE Air-Filled (CHDL< 1" w/o internal spacer) -- Produced with capillary tubes	0.29	0.21	0.36	59	X
Triple IG -- LE/CL/CL Argon-Filled	0.30	0.26	0.47	60	X
Triple IG -- LE/CL/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.23	0.42	60	X
Triple IG -- LE/CL/LE Argon-Filled	0.26	0.23	0.40	60	X
Triple IG -- LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.26	0.21	0.36	60	X
<i>Note--CHDL in Triple IG cannot be ordered with internal spacer.</i>					

<b>Monument Single Hung/Double Hung Operator (1" Triple IG -- Not Available With GIAS or Internal HDL Spacer Bar; Some Size Limitations Apply)</b>					
Triple IG -- LE/CL/LE Air-Filled -- Produced with capillary tubes	0.30	0.23	0.39	59	X
Triple IG -- LE/CL/LE Air-Filled (CHDL< 1" w/o internal spacer) -- Produced with capillary tubes	0.30	0.20	0.34	59	X
Triple IG -- LE/CL/CL Argon-Filled	0.30	0.25	0.45	60	X
Triple IG -- LE/CL/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.22	0.40	60	X
Triple IG -- LE/CL/LE Argon-Filled	0.27	0.23	0.39	60	X
Triple IG -- LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.27	0.20	0.34	60	X
<i>Note--CHDL in Triple IG cannot be ordered with internal spacer.</i>					

<b>Monument Picture (3/4" IG)</b>					
Insul LE/CL Argon-Filled	0.30	0.29	0.52	56	X
Insul LE/CL Argon-Filled (w/GIAS or CHDL< 1")	0.30	0.26	0.46	55	X
Insul LE SPF/CL Argon-Filled	0.30	0.29	0.51	56	X
Insul LE SPF/CL Argon-Filled (w/GIAS or CHDL< 1")	0.30	0.26	0.45	55	X
Insul--Super Sunblocker LE/CL Argon-Filled	0.30	0.21	0.40	56	X
Insul--Super Sunblocker LE/CL Argon-Filled (w/GIAS or CHDL< 1")	0.30	0.19	0.36	56	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled	0.30	0.21	0.39	56	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled (w/GIAS or CHDL< 1")	0.30	0.19	0.35	56	X
Insul--Cardinal 366 LE/CL Argon-Filled	0.29	0.21	0.47	60	X
Insul--Cardinal 366 LE/CL Argon-Filled (w/GIAS or CHDL< 1")	0.30	0.19	0.42	60	X
<i>Note--CHDL in Triple IG cannot be ordered with internal spacer.</i>					

<b>Monument Picture (1" Triple IG -- Not Available With GIAS or Internal HDL Spacer Bar; Some Size Limitations Apply)</b>					
Triple IG -- LE/CL/LE Air-Filled -- Produced with capillary tubes	0.27	0.24	0.39	60	X
Triple IG -- LE/CL/LE Air-Filled (CHDL< 1" w/o internal spacer) -- Produced with capillary tubes	0.27	0.21	0.35	60	X
Triple IG -- LE/CL/CL Argon-Filled	0.28	0.26	0.46	60	X
Triple IG -- LE/CL/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.28	0.23	0.41	60	X
Triple IG -- LE/CL/LE Argon-Filled	0.23	0.24	0.46	60	X
Triple IG -- LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.23	0.21	0.41	60	X
<i>Note--CHDL in Triple IG cannot be ordered with internal spacer.</i>					

<b>Monument Sash &amp; Frame (3/4" IG)</b>					
Insul LE/CL Argon-Filled	0.30	0.30	0.55	56	X
Insul LE/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.27	0.49	55	X
Insul--Super Sunblocker LE/CL Argon-Filled	0.30	0.22	0.42	56	X
Insul--Super Sunblocker LE/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.20	0.38	56	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled	0.30	0.21	0.41	56	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.20	0.37	56	X
Insul--Cardinal 366 LE/CL Argon-Filled	0.29	0.22	0.50	59	X
Insul--Cardinal 366 LE/CL Argon-Filled (w/GIAS or CHDL< 1")	0.30	0.26	0.48	58	X
<i>Note--CHDL in this product cannot be ordered with internal spacer as it will not meet the tax credit requirements</i>					

<b>Monument Sash &amp; Frame (1" Triple IG -- Not Available With GIAS or Internal HDL Spacer Bar)</b>					
Triple IG -- LE/CL/LE Air-Filled -- Produced with capillary tubes	0.26	0.25	0.42	64	X
Triple IG -- LE/CL/LE Air-Filled (CHDL< 1" w/o internal spacer) -- Produced with capillary tubes	0.26	0.22	0.38	64	X
Triple IG -- LE/CL/CL Argon-Filled	0.27	0.27	0.49	63	X
Triple IG -- LE/CL/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.27	0.24	0.44	63	X
Triple IG -- LE/CL/LE Argon-Filled	0.23	0.25	0.42	67	X
Triple IG -- LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.23	0.22	0.38	67	X
<i>Note--CHDL in Triple IG cannot be ordered with internal spacer.</i>					

Hurd Clad Wood Products That Qualify for 2009/2010 Tax Credit

PRODUCT/GLAZING MAKE-UP	U-FACTOR	SHGC	VT	CR	QUALIFIES FOR TAX CREDIT
<b>Energy Saver Direct Set (3/4" IG)</b>					
Insul--Climate Control LE/CL Argon-Filled (GIAS and CHDL< 1")	0.30	0.30	0.54	52	X
Insul--Climate Control SPF LE/CL Argon-Filled (GIAS and CHDL< 1")	0.30	0.29	0.53	50	X
Insul--Super Sunblocker LE/CL Argon-Filled	0.29	0.25	0.48	53	X
Insul--Super Sunblocker LE/CL Argon-Filled (GIAS and CHDL< 1")	0.30	0.23	0.43	52	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled	0.29	0.24	0.47	53	X
Insul--Super Sunblocker LE/CL Argon-Filled (GIAS and CHDL< 1")	0.30	0.22	0.42	52	X
Insul--Cardinal 366 LE/CL Argon-Filled	0.28	0.25	0.56	55	X
Insul--Cardinal 366 LE/CL Argon-Filled (GIAS and CHDL< 1")	0.30	0.22	0.51	55	X
<b>Energy Saver Direct Set (1" Triple IG -- Not Available With GIAS or Internal HDL Spacer Bar)</b>					
Triple IG -- LE/CL/LE Air-Filled -- Produced with capillary tubes	0.28	0.28	0.48	58	X
Triple IG -- LE/CL/LE Air-Filled (CHDL< 1" w/o internal grilles) -- Produced with capillary tubes	0.28	0.25	0.43	58	X
Triple IG -- LE/CL/CL Argon-Filled	0.28	0.30	0.55	58	X
Triple IG -- LE/CL/CL Argon-Filled (CHDL< 1" w/o internal grilles)	0.28	0.28	0.50	58	X
Triple IG -- LE/CL/LE Argon-Filled	0.24	0.28	0.48	58	X
Triple IG -- LE/CL/LE Argon-Filled (CHDL< 1" w/o internal grilles)	0.24	0.26	0.43	58	X
<i>Note--CHDL in Triple IG cannot be ordered with internal spacer.</i>					
<b>Energy Saver Direct Set Circle Top (3/4" IG)</b>					
Insul--Climate Control LE/CL Argon-Filled (GIAS and CHDL< 1")	0.30	0.30	0.54	52	X
Insul--Climate Control SPF LE/CL Argon-Filled (GIAS and CHDL< 1")	0.30	0.29	0.53	52	X
Insul--Super Sunblocker LE/CL Argon-Filled	0.29	0.25	0.48	53	X
Insul--Super Sunblocker LE/CL Argon-Filled (GIAS and CHDL< 1")	0.29	0.23	0.43	52	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled	0.29	0.24	0.47	52	X
Insul--Super Sunblocker SPF LE/CL Argon-Filled (GIAS and CHDL< 1")	0.29	0.22	0.42	52	X
Insul--Cardinal 366 LE/CL Argon-Filled	0.28	0.25	0.56	57	X
Insul--Cardinal 366 LE/CL Argon-Filled (GIAS and CHDL< 1")	0.28	0.22	0.51	56	X
<b>Energy Saver Direct Set Circle Top (1" Triple IG -- Not Available With GIAS or Internal HDL Spacer Bar)</b>					
Triple IG -- LE/CL/LE Air-Filled -- Produced with capillary tubes	0.28	0.28	0.48	58	X
Triple IG -- LE/CL/LE Air-Filled (CHDL< 1" w/o internal spacer) -- Produced with capillary tubes	0.28	0.25	0.43	58	X
Triple IG -- LE/CL/CL Argon-Filled	0.28	0.30	0.56	58	X
Triple IG -- LE/CL/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.28	0.28	0.50	58	X
Triple IG -- LE/CL/LE Argon-Filled	0.24	0.28	0.48	58	X
Triple IG -- LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.24	0.25	0.43	58	X
<i>Note--CHDL in Triple IG cannot be ordered with internal spacer.</i>					
<b>Energy Saver Standard Sliding Patio Door (3/4" IG)</b>					
Insul--Cardinal 366 LE/CL Argon-Filled	0.30	0.21	0.49	57	X
Insul--Cardinal 366 LE/CL Argon-Filled (w/GIAS or CHDL< 1")	0.30	0.19	0.43	57	X
<i>Note--CHDL in this product cannot be ordered with internal spacer as it will not meet the tax credit requirements</i>					
<b>Energy Saver Sliding Patio Door (1" Triple IG -- Not Available With GIAS or Internal HDL Spacer Bar)</b>					
Triple IG--LE/CL/LE Argon-Filled	0.27	0.24	0.41	59	X
Triple IG--LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.27	0.21	0.36	59	X
<i>Note--CHDL in this product cannot be ordered with internal spacer.</i>					
<b>Energy Saver French Sliding Patio Door (1" Triple IG -- Not Available With GIAS or Internal HDL Spacer Bar)</b>					
Triple IG--LE/CL/LE Argon-Filled	0.28	0.20	0.34	60	X
Triple IG--LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.28	0.18	0.30	60	X
<i>Note--CHDL in Triple IG cannot be ordered with internal spacer.</i>					
<b>Energy Saver Inswing Patio Door (1" Triple IG -- Not Available With GIAS or Internal HDL Spacer Bar)</b>					
Triple IG--LE/CL/LE Air-Filled -- Produced with capillary tubes	0.30	0.20	0.31	60	X
Triple IG--LE/CL/LE Air-Filled (CHDL< 1" w/o internal spacer) -- Produced with capillary tubes	0.30	0.17	0.27	60	X
Triple IG--LE/CL/CL Argon-Filled	0.30	0.22	0.37	60	X
Triple IG--LE/CL/CL Argon-Filled (CHDL< 1" w/o internal spacer)	0.30	0.19	0.31	60	X
Triple IG--LE/CL/LE Argon-Filled	0.27	0.15	0.31	60	X
Triple IG--LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.27	0.17	0.27	60	X
<i>Note--CHDL in Triple IG cannot be ordered with internal spacer.</i>					
<b>Energy Saver Outswing Patio Door (1" Triple IG -- Not Available With GIAS or Internal HDL Spacer Bar)</b>					
Triple IG--LE/CL/LE Air-Filled -- With capillary tubes (French version does not meet tax credit)	0.30	0.20	0.33	59	X
Triple IG--LE/CL/LE Air-Filled (CHDLw/o internal spacer) -- With capillary tubes (French version does not meet tax credit)	0.30	0.17	0.28	59	X
Triple IG--LE/CL/LE Argon-Filled	0.28	0.20	0.31	60	X
Triple IG--LE/CL/LE Argon-Filled (CHDL< 1" w/o internal spacer)	0.28	0.17	0.26	60	X
<i>Note--CHDL in Triple IG cannot be ordered with internal spacer.</i>					

Hurd Clad Wood Products That Qualify for 2009/2010 Tax Credit

PRODUCT/GLAZING MAKE-UP	U-FACTOR	SHGC	VT	CR	QUALIFIES FOR TAX CREDIT
-------------------------	----------	------	----	----	--------------------------

Hurd Clad Wood Products That Qualify for 2009/2010 Tax Credit

PRODUCT/GLAZING MAKE-UP	U-FACTOR	SHGC	VT	CR	QUALIFIES FOR TAX CREDIT
<b>H-3 Casement Operator (3/4" IG)</b>					
Insul--LE/CL Argon-Filled w/Stainless Steel Spacer <sup>†</sup>	0.30	0.29	0.52	54	X
Insul--LE/CL Argon-Filled (w/GIA or CHDL<1" with or w/o internal spacer) w/Stainless Steel Spacer <sup>†</sup>	0.30	0.27	0.48	54	X
Insul--Super Sunblocker LE/CL Argon-Filled w/Stainless Steel Spacer <sup>†</sup>	0.30	0.21	0.40	54	X
Insul--Super Sunblocker LE/CL Argon-Filled (w/GIA or CHDL<1" with or w/o internal spacer) w/Stainless Steel Spacer <sup>†</sup>	0.30	0.19	0.37	54	X
Insul--Cardinal 366 LE/CL Argon-Filled	0.29	0.21	0.48	57	X
Insul--Cardinal 366 LE/CL Argon-Filled (w/GIA or CHDL<1" with or w/o internal spacer)	0.29	0.19	0.43	56	X
<sup>†</sup> This product requires you to request "w/SS Spacer and Argon"					
<b>H-3 Casement Picture (3/4" IG)</b>					
Insul--LE/CL Argon-Filled (w/GIA or CHDL<1" with or w/o internal spacer)	0.29	0.29	0.52	49	X
Insul--Climate Control LE/CL Argon-Filled	0.29	0.30	0.51	50	X
Insul--Climate Control LE/CL Argon-Filled (w/GIA or CHDL< 1")	0.29	0.28	0.51	49	X
Insul--Super Sunblocker/CL Argon-Filled	0.28	0.23	0.45	50	X
Insul--Super Sunblocker LE/CL Argon-Filled (w/GIA or CHDL< 1" with or w/o internal spacer)	0.28	0.21	0.40	50	X
Insul--Cardinal 366 LE/CL Argon-Filled	0.27	0.23	0.53	55	X
Insul--Cardinal 366 LE/CL Argon-Filled (w/GIA or CHDL< 1" with or w/o internal spacer)	0.27	0.21	0.48	55	X
<b>H-3 Awning Operator (3/4" IG)</b>					
Insul--LE/CL Argon-Filled w/Stainless Steel Spacer <sup>†</sup>	0.30	0.29	0.52	53	X
Insul--LE/CL Argon-Filled (w/GIA or CHDL<1" with or w/o internal spacer) w/Stainless Steel Spacer <sup>†</sup>	0.30	0.27	0.48	53	X
Insul--Super Sunblocker LE/CL Argon-Filled w/Stainless Steel Spacer <sup>†</sup>	0.30	0.21	0.40	53	X
Insul--Super Sunblocker LE/CL Argon-Filled (w/GIA or CHDL<1" with or w/o internal spacer) w/Stainless Steel Spacer <sup>†</sup>	0.30	0.19	0.37	53	X
Insul--Cardinal 366 LE/CL Argon-Filled	0.29	0.21	0.48	56	X
Insul--Cardinal 366 LE/CL Argon-Filled (w/GIA or CHDL<1" with or w/o internal spacer)	0.29	0.19	0.43	56	X
<sup>†</sup> This product requires you to request "w/SS Spacer and Argon"					